

NOTES:


MATERIAL:

HOUSING: BLUE THERMOPLASTIC POLYESTER, UL94V-0 STEEL, TIN PLATED SHELL: CONTACT: COPPER ALLOY, 15µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT CONTACT RESISTANCE: $25m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

				SW REFERENCE NO.: 628M ASSEMBLY		
			DRAWN: C.B	DATE: AUG. 01/20)18	
			CHECKED:	DATE:		
	EDAC INC	OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS	SCALE: 1:1	SHEET 1 OF	1	
	EDAC INC TORONTO, ONTARIO CANADA		DRAWING NUMBER: 628-M25	G NUMBER: 628-M25-321-LT5		
	YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER: 628-M25	-321-LT5	1	





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.