


10.7 ±0.3 5.80 5.1 ±0.3

.XX ±0.13 .XXX ±0.10



NOTES:


MATERIAL:

HOUSING: WHITE THERMOPLASTIC POLYESTER, UL94V-0 STEEL, NICKEL PLATED SHELL: CONTACT: COPPER ALLOY, 15µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT CONTACT RESISTANCE: $25m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
628 SERIES D			DATE: AUG. 01/20	018	
			DATE:		
EDAC INC	NC THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND	SCALE: 1:1	SHEET 1 OF	1	
	OR USED AS THE BASIS FOR THE	DRAWING NUMBER: 628-M25-321-WN3		ISSUE	
YOUR CONNECTION TO QUALITY & SE	ERVICE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	PART NUMBER: 628-M25	5-321-WN3	1	





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.