



10.7 ±0.3

5.80










.XX ±0.13 .XXX ±0.10



NOTES:


MATERIAL:

HOUSING: GREEN THERMOPLASTIC POLYESTER, UL94V-0 STEEL, NICKEL PLATED SHELL: CONTACT: COPPER ALLOY, GOLD FLASH PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT $25m\Omega$ MAX. CONTACT RESISTANCE: INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY				
			DRAWN: C.B		DATE: AUG. 01/2018		I
			CHECKED:		DATE:		1
	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1		SHEET 1 OF	1	1
	TORONTO, ONTARIO CANADA		DRAWING NUMBER:	628-M25-221-GN4		ISSUE	1
	YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER:	628-M25-	221-GN4	1	1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.