




.XX ±0.13 .XXX ±0.10









10.7 ±0.3 5.80 5.1 ±0.3



NOTES:

MATERIAL:

HOUSING:GREEN THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, TIN PLATEDCONTACT:COPPER ALLOY, 30µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
628 SERIES D-SUB			DATE: AUG. 01/20)18	
			DATE:		
EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1	
TORONTO, ONTARIO CANADA		DRAWING NUMBER: 628-M15-621-GT1		ISSUE	
YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER: 628-M15	-621-GT1	1	



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.