


.XX ±0.13 .XXX ±0.10




NOTES:

MATERIAL:

HOUSING:WHITE THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, NICKEL PLATEDCONTACT:COPPER ALLOY, 15µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
			DRAWN: C.B	DATE: AUG. 01/20	018
			CHECKED:	DATE:	
	EDAG INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1
			DRAWING NUMBER: 628-M37	-321-WN1	ISSUE
			PART NUMBER: 628-M37	-321-WN1	1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.