



General ordering data

Order No.	1783680000
Part designation	LX 15.00/3/90 GR
Version	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 3, 90°, Box
EAN	4032248184934
Qty.	20 pc(s).

System parameters

Product family	System LX
Conductor connection system	Clamping yoke connection
Fitted to PCB	Soldered connection
Outgoing direction of conductor	90°
Pitch	15 mm
Pitch in inch	0.591 inch
No. of poles	3
Fitted by customer	no
Max. adjacent poles per row	10
No. of rows	1
Solder pin length	4.5 mm
Dia. of fitting hole	1.6 mm
Fitting hole tolerance	+ 0.1 mm
No. of solder pins per pole	2

System parameters

Screwdriver blade	1.0 x 5.5
Screwdriver blade standard	DIN 5264
Tightening torque, min.	2 Nm
Tightening torque, max.	4 Nm
Clamping screw	M 5
Stripping length	16 mm
L1 in mm	30 mm
L1 in inch	1.181 inch
Electric shock protection to DIN VDE 0470	IP 10
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	Wemid (PA)
Colour	pebble grey
colour chart	Similar to RAL 7032
Insulating material group	I
Flammability class UL 94	V-1
CTI	>= 601
Temperature of glow-wire test	960 °C
Duration of glow-wire test	30 S
Contact base material	E-Cu
Contact surface	tinned
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C

Connectable conductors

Clamping range, min.	1.31 mm ²
Clamping range, max.	25 mm ²
AWG, min.	16
AWG, max.	4
Solid, min. H05(07) V-U	1.5 mm ²
Solid, max. H05(07) V-U	16 mm ²
Stranded, min. H07V-R	6 mm ²
Stranded, max. H07V-R	25 mm ²
Flexible, min. H05(07) V-K	1.5 mm ²
Flexible, max. H05(07) V-K	25 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	1.5 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	16 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	1.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	16 mm ²
Gauge to EN 60999 a x b; ø	6.9 mm x 6.9 mm

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	101 A
Rated current, max. No. pins (Tu=20°C)	101 A
Rated current, min. No. pins (Tu=40°C)	101 A
Rated current, max. No. pins (Tu=40°C)	101 A
Rated voltage for overvoltage class/pollution severity II/2	1,000 V
Rated voltage for overvoltage class/pollution severity III/2	1,000 V

DIN IEC rating data

Rated voltage for overvoltage class/pollution severity III/3	1,000 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	6 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	8 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	8 kV
Short-time withstand current resistance	3 x 1s mit 1000 A

CSA rating data

Rated current (Use group C)	85 A
Rated voltage (Use group C)	600 V
Rated voltage (Use group D)	600 V
Rated current (Use group D)	5 A
AWG conductor (field wiring), min.	16
AWG conductor (field wiring), max.	4

UL 1059 rating data

Rated voltage (Use group C)	600 V
Rated current (Use group C)	85 A
Rated voltage (Use group D)	600 V
Rated current (Use group D)	5 A
AWG conductor, min.	16
AWG conductor, max.	4

Approvals

Approvals institutes

**Downloads**

CAD Library (P-CAD Format - Standard)	LX.lib
---------------------------------------	--------

Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

Similar products

Order No.	Part designation	Version
1783660000	LX 15.00/1/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 1, 90°, Box
1783670000	LX 15.00/2/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 2, 90°, Box
1783760000	LX 15.00/3/90 GN	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 3, 90°, Box
1783690000	LX 15.00/4/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 4, 90°, Box
1806460000	LX 15.00/5/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 5, 90°, Box
1809870000	LX 15.00/6/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 6, 90°, Box
1809880000	LX 15.00/8/90 GR	PCB terminal, Clamping yoke connection, Soldered connection, Clamping range, max.: 25 mm ² , Pitch: 15.00 mm, No. of poles: 8, 90°, Box