


10.7 ±0.3 5.80 5.1 ±0.3

.XX ±0.13 .XXX ±0.10



NOTES:

MATERIAL:

HOUSING:WHITE THERMOPLASTIC POLYESTER, UL94V-0SHELL:STEEL, TIN PLATEDCONTACT:COPPER ALLOY, 15µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

		SW REFERENCE NO.: 628M ASSEMBLY					
628 SERIE	628 SERIES D-SUB CONNECTOR			DRAWN: C.B		DATE: AUG. 01/2018	
			CHECKED:		DATE:		
	DAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND	VINGS AND SPECIFICATIONS OPERTY OF EDAC INC.,AND SE REPROVINCED OR COPIED				
	TORONTO, ONTARIO CANADA QUALITY & SERVICE	SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 628-M25-3		-321-WT4		ISSUE
YOUR CONNECTION TO QUALIT			PART NUMBER:	628-M25-	321-WT4		1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.