<u>Contact Dimensions:</u>
544-Wire Wrap .050x.025(1.27x0.64) - Tail LG=.750(19.05)
.100 (2.54) Contact Spacing x .200 (5.08) Row Spacing 1 -2x Ø.156[3.96] -7.000 [177.8] -7.160[181.86] -7.475 [189.87] .330[8.38] CARD SLOT 160[4.06] POINT OF CONTACT 600 [15.24] 7.735 [196.47] **SECTION A-A** ACAD REFERENCE NO. 345-ENG-MASTER 345/395 SERIES CARD EDGE CONNECTOR DRAWN: R.STA.MONICA DATE:MAY.16/2017 PART NUMBER: 395-138-544-208 INSULATOR MATERIAL: THERMOPLASTIC PBT BLACK, UL 94V-0 1:1 SHEET 1 OF 2 CONTACT MATERIAL; COPPER TIN ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING

YOUR CONNECTION TO QUALITY & SERVICE

345-ENG-MASTER

ON THE CONTACT TAILS, NICKEL UNDERPLATE











Contact Code 558

Contact Code 559

Contact Code 560

INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL 94V-0

DAP MATERIAL AVAILABLE UPON REQUEST

CONTACT MATERIAL; COPPER ALLOY CONTACT PLATING: GOLD ON THE MATING AREA, TIN PLATING ON THE CONTACT TAILS, NICKEL UNDERPLATE

345/395 SERIES CARD EDGE CONNECTOR CONTACT CODE 555,556,558,559,560 DIMENSIONS

YOUR CONNECTION TO QUALITY & SERVICE

ACAD REFERENCE NO. 345-ENG-MASTER DATE:MAY.16/2017 DRAWN: R.STA.MONICA 1:1 SHEET 2 OF 2 345-ENG-MASTER