




**SPECIFICATIONS**  
 Current Rating: 9A AC,DC  
 Voltage Rating: 600V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 10mΩ Max  
 Insulation Resistance: 1000MΩ Min  
 Withstanding Voltage: 1500V AC/minute  
 Pin Material: Brass/Tin-plated  
 Material: Nylon 66,UL94V-2  
 Color: Natural(Translucent)



P.C.B LAYOUT

PART NO.	Dimensions	
	A	B
2X01	---	5.40
2X02	4.20	9.60
2X03	8.40	13.80
2X04	12.60	18.00
2X05	16.80	22.20
2X06	21.00	26.40
2X07	25.20	30.60
2X08	29.40	34.80
2X09	33.60	39.00
2X10	37.80	43.20
2X11	42.00	47.40
2X12	46.20	51.60

APPROVALS		DATE
DRAWN	G.M.Chen	2015/5/29
CHECKED		
APPROVALS		
TITLE: 4.20mm Crimp Style Connectors PART NO. X4020WR-XXA UNIT: mm SCALE: 1:1 SHEET 1 OF 1 DRAWING NO. PROJ.		
TOLERANCES ARE: 30~40H±0.30 ANGLE ±2° 10~30H±0.20 5~10H±0.15 ~5H±0.10		
ECN NO.	REV.	DATE.
	A	
DESCRIPTION. NEW		
CHANGE.	CHECK.	APPRO.

德之隆

DEALON 德之隆  
 ELECTRONICS CO.,LTD