


PART NO.	Dimensions	
	A	B
2X01	---	5.40
2X02	4.20	9.60
2X03	8.40	13.80
2X04	12.60	18.00
2X05	16.80	22.20
2X06	21.00	26.40
2X07	25.20	30.60
2X08	29.40	34.80
2X09	33.60	39.00
2X10	37.80	43.20
2X11	42.00	47.40
2X12	46.20	51.60

APPROVALS		DATE	PART NO.		SCALE	SHEET
DRAWN	G.M.Chen	2015/5/29	X4020WV-XXA		1:1	1 OF 1
CHECKED						
APPROVALS						
TOLERANCES ARE: 30 ^{±0.15} ±0.30 ANGLE ±2° 10 ^{±0.10} ±0.20 5 ^{±0.05} ±0.15						
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.	CHECK.
	A		NEW			


DEALON 德之隆
ELECTRONICS CO., LTD

SPECIFICATIONS


Current Rating: 9A AC,DC
 Voltage Rating: 600V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Pin Material: Brass/Tin-plated **PA66**
 Material: **PA66**




2X1P




2X2P




2X3P




2X4P




2X5P




2X6P




2X7P




2X8P




2X9P



2X10P



2X11P



2X12P

PART NO.	Dimensions	
	A	B
2X01	---	5.40
2X02	4.20	9.60
2X03	8.40	13.80
2X04	12.60	18.00
2X05	16.80	22.20
2X06	21.00	26.40
2X07	25.20	30.60
2X08	29.40	34.80
2X09	33.60	39.00
2X10	37.80	43.20
2X11	42.00	47.40
2X12	46.20	51.60

APPROVALS		DATE
DRAWN	G.M.Chen	2015/5/29
CHECKED		
APPROVALS		

DEALON 德之隆
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30 ^{±0.15} 10 ^{±0.30} 5 ^{±0.10}	±0.30 ±0.20 ±0.15	ANGLE	±2°	PART NO.	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
	A		NEW									X4020WV-XXA			
															PROJ.