



Bestückungsplan / contact layout



Tauchlötanschluss 0,65 x 0,3 mm / solder terminal 0,65 x 0,3 mm
 Isolierwerkstoff / housing material : PBT GF 30
 Bauart 7 / type 7
 Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
 Fehlende Masse und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
 Missing Information and dimensions per IEC 60 603-2

Leiterplatten-Lochbild / PCB drillhole Pattern



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustererhaltung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.
 Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen von dem englischen Original gilt das englische Original. The german version of this drawing has been offered for convenience only and may deviate from the english original. In case of any deviation the English version shall prevail.

Dimension no.	Tolerances	All Dimensions in mm	Scale 2:1
Customer drawing:	ISO 8015	Subject to modification without prior notice. Drawing will not be updated.	Material
This Drawing is a controlled Document.			Federleiste C/2 48 Löt Fem. Connector C/2 48 Solder
			284174
a	17.05.2011		1
Index	Date		A3
		Class	STVC/2