

10 Watts

AEE01,02

Total Power: 10 Watts
Input Voltages: 48V, 24V
No. of Outputs: Single



Special Features

- 10 W, Single output
- 2:1 Input range
- 1.0" x 2.0" x 0.33 case
- Replaces AA10B
- Industry standard package
- Low Profile
- Low Cost

Environmental

Operating base temperature range:

-25°C to +95°C

Storage temperature: -40°C to +105°C

MTBF: 3 Million Hours (Belcore TR332)

Safety

UL UL1950 Recognition

CSA CSA22.2-950 Recognition

TUV EN60950 Recognition

Electrical Specs

Input

Input range 18 to 36 VDC
36 to 72 VDC

Efficiency 79% typical (5V)

Output

Voltage tolerance $\pm 1.0\%$ ($\pm 2.0\%$ for 3.3V)

Overall regulation $\pm 1\%$ max

Noise/ripple 1% (mV P-P)

Transient response 200 usec typical (50% step load change to within 5%Vo)

Temperature Regulation $\pm 0.02\%$ Vo/°C

Switching frequency 330kHz

Isolation

I/O isolation 500 VDC

Isolation Resistance 300 Mohms

AMERICAS

5810 Van Allen Way
 Carlsbad, CA 92008
 Telephone: 760-930-4600
 Facsimile: 760-930-0698

EUROPE

Astec House, Waterfront Business Park
 Merry Hill, Dudley
 West Midlands, DY5 1LX, UK
 Telephone: 44 (1384) 842-211
 Facsimile: 44 (1384) 843-355

ASIA


Units 2111-2116, Level 21
 Tower1, Metroplaza
 223, Hing Fong Road
 Fwai Fong, New Territories
 Hong Kong
 Telephone: 852-2437-9662
 Facsimile: 852-2402-4426



Ordering Information

Input Voltage	Output Voltage	Efficiency	Model Number
18-36 V	3.3 @ 2.5 A	76%	AEE02F24
18-36 V	5.0 @ 2.0 A	78%	AEE02A24
18-36 V	8.0 @ 1.25A	78%	AEE01L24
18-36 V	12.0 @ 0.84 A	82%	AEE00B24
18-36 V	15.0 @ 0.67 A	82%	AEE00C24
36-72 V	3.3 @ 2.5 A	77%	AEE02F48
36-72 V	5.0 @ 2.0 A	79%	AEE02A48
36-72 V	8.0 @ 1.25 A	77%	AEE01L48
36-72 V	12.0 @ 0.84 A	84%	AEE00B48
36-72 V	15.0 @ 0.67 A	86%	AEE00C48

Mechanical Dimensions and Pin Assignments



Notes:

1. 20 MHz bandwidth. An external 0.1 uf ceramic capacitor is recommended to be placed from +V out to comm.
2. All specifications are typical at nominal line, full load, and 25°C unless otherwise noted.
3. All specifications subject to change without notice.
4. Mechanical drawings are for reference only.