







# CLF6045T-101M-CA

Applications		Automotive Grade
Feature		Wire Wound
		Magnetic Shield
		Ferrite Core
		AEC-Q200
Series	CLF-CA Series / CLF6045-CA Type	
Status	PROD	



Size	
Length(L)	6.20mm +/-0.20mm
Width(W)	5.90mm +/-0.20mm
Thickness(T)	4.50mm +/-0.30mm
Recommended Land Pattern (A)	1.70mm Nom.
Recommended Land Pattern (B)	3.60mm Nom.
Recommended Land Pattern (C)	2.20mm Nom.


Electrical Characteristics	
Inductance	100uH +/-20% at 100kHz
Rated Current (L Change) [Typ.]	640mA (10% Down)
Rated Current (Temperature Rise) [Typ.]	700mA (30degC Rise)
DC Resistance [Nom.]	340mΩ
DC Resistance [Max.]	408mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 105degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	Yes
Packing	Blister (Plastic)Taping [330mm Reel]
Package Quantity	1000Pcs Min.
Weight	0.6g


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# CLF6045T-101M-CA


**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




CLF6045T-101M-CA



CLF6045T-101M-CA



CLF6045T-101M-CA




CLF6045T-101M-CA


•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.

# CLF6045T-101M-CA

**Characteristic Graphs** (This is reference data, and does not guarantee the product's characteristics.)




CLF6045T-101M-CA(Amb. Temp. = 20degc)



CLF6045T-101M-CA(DC = 0A)

CLF6045T-101M-CA(DC = 0.32A)



CLF6045T-101M-CA(Amb. Temp. = 20degc)

•This PDF document was created based on the data listed on the TDK Corporation website.  
 •All specifications are subject to change without notice.