

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A		NEW	C.W	23.04.12





NOTES1:
 UL Standard
 1.Rated voltage/current : 300V / 8A
 2.Withstanding voltage : AC1500V/1Min.
 3.Wire range : 28~16AWG

IEC Standard

1. Pollution degree	2
Overvoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	8A

2.Wire diameter range : 0.2~1.0mm²
 NOTES2:
 1.Dimension shall be interpreted per ASME Y14.5-2009
 2.Pitch : 3.81mm, Poles : N=02~24P
 3.Stripping length : 10mm
 4.Operating temperature:-40°C~+105°C
 5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm				Tolerances	
TO	Over	Over	TO	Over	Over	Over	0.1/10	
6	10	24	30	60	100	150		±2°
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	



5.RoHS Compliance

Ordering Information

JL15EDGKN - 1000A - 381 XX X X 1

- Pitch: 381=3.81PH
- No.of pins: 2P~24P
- Housing Color: B=Black, G=Green(Convention), U=Blue, R=Red, W=White, Y=Yellow, O=Orange, E=Grey
- Packing: 0=Pe bag, A=Tray, T=Tube

DRAW		SCALE	FIT	东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
CHECK		UNIT	mm		
APPROVE		SHEET	1/1	PART NO.	JL15EDGKN-1000A-381XXXX1
		PROJ.		TITLE:	JL15EDGKN-3.81-1000A-XXP插拔式母座/方形按钮