





HOOYA



电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk
 V : hooya89

皓宇电子
 HOOYA ELECTRONICS

| | | | | | | | | | | | | |
|-----|------|-------|----------|--------------|--|-------------|----|------------|---|---|---------|------|
| | | | | | TOLERANCE UNLESS SPECIFIED | | | | | | | |
| | | | | | UP TO 5mm: ±0.1 | ANGULAR ±1° | A1 | 2019.5.22 | 更新图纸 | | XYZ | |
| | | | | | ABOVE 5mm: ±0.2 | | NO | DATE | REVISIONS | | BY | APPD |
| | | | | | TITLE: | | | UNIT : MM | ROHS COMPLIANT | DWN | | |
| | | | | | MODEL: HY-DC16540-22.0A("A"带冲) | | | SCALE: 1:1 | | CHK'D | | |
| 3 | A14 | PBS | 1 | NI-PLATED |  HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司 | | | APPD | | | | |
| 2 | 016冲 | BRASS | 1 | NI-PLATED | | | | | | | | |
| 1 | 注塑 | POM | 1 | BLACK/YELLOW | | | | | | | | |
| NO. | PART | NAME | MATERIAL | QTY | FINISHING | | | PRO.AGL: |  |  | REV :A1 | |