


电话：0769-82310511-867  
 邮箱：hooya89@hooya.hk  
 V：hooya89  
 HOOYA ELECTRONICS



PCB LAYOUT

SPECIFICATION

1. Rating : DC30V 1.5A.
2. Contact resistance:  $\leq 100m\Omega$ .
3. Insulation resistance:  $\geq 1000M\Omega$  (DC500V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 10-35N.
6. life test: 5000 cycles.
7. Operation temperature range:  $-25^{\circ}C \sim 85^{\circ}C$ .

				TOLERANCE		A3	2023.11.23	增加电镀层	WM		
				UNLESS SPECIFIED		A2	2023.4.18	更新图纸	WM		
				< 1.5: ±0.1mm	ANGULAR ±1°	A1	2023.3.7	更新材质	WM		
				> 1.5~5.0: ±0.25mm		NO	DATE	REVISIONS		BY	APPD
				> 5.0: ±0.3mm							
				TITLE: USB JACK			UNIT : MM	ROHS COMPLIANT	DWN		
				MODEL: USB-111LH-B-SU B型 T.2.5			SCALE: 1:1	CHK'D			
				DONGGUANG HAOYU ELECTRONICS CO., LTD			APPD				
				东莞市弘皓电子有限公司			PRO.AGL:	⊲	⊕	REV :A3	
3	CONTACT FOOT	PHOSPHOR BRONZE	5	1u"Au-Plated							
2	SHELL	SUS	1	50u"Sn-Plated							
1	HOUSING	LCP(UL94V-0)	1								
NO.	PART NAME	MATERIAL	QTY	FINISHING							