



Circuit Diagram

PCB Layout (Pattern side)

Note:  
 1. Rating: 30V 0.1A  
 2. Operating Force: 50g Max

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Contact Spring	1	Phosphor Bronze	Ag Plated
④	Terminal	4	Phosphor Bronze	Ag Plated
③	Base	1	NYLON	Black
②	Cover	1	NYLON	Black
①	Slider	1	NYLON	White

APPROVALS		DATE	PART NO.		SCALE	SHEET
DRAWN	G.M.Chen	2014/11/20	TK-1040-A	1:1	1 OF 1	
CHECKED						
APPROVALS						
TOLERANCES ARE		30 <sup>±0.15</sup>	±0.30	ANGLE		
		10 <sup>±0.10</sup>	±0.20	UNIT: mm		
		5 <sup>±0.10</sup>	±0.15	DRAWING NO.		
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

**DEALON 德之隆**  
 ELECTRONICS CO., LTD

TITLE: DETECTOR SWITCHES