




Note:
 1. Rating: 12V 0.1A
 2. Operating Force: 0.5N Max



⑥	Slider	1	PA66	Black
⑤	Base	1	PA66	Black
④	Spring	1	Brass(0.05t)	Plating silver
③	Contact	1	SUS	
②	Cover	1	PC	Transparent
①	Terminal	1	Brass(0.2t)	Plating silver
ITEM	PART NAME	QTY.	MATERIAL	FINISHING

APPROVALS		DATE	TITLE:
DRAWN	G.M.Chen	2014/8/18	ELECTRONICS CO.,LTD
CHECKED			
APPROVALS			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30 ^{±0.1} ±0.30	±2°	mm	1:1	1 OF 1	
							10 ^{±0.10} ±0.20					
							5 ^{±0.10} ±0.15					
							~5					

DEALON 德之隆
 ELECTRONICS CO.,LTD

TK-2060-A
 DETECTOR SWITCHES