



TECHNICAL CHARACTERISTICS

MATERIAL  
 INSULATOR: PA66  
 FLAMMABILITY RATING: UL94-V0  
 COLOR: GREEN  
 CONTACT: BRASS  
 SOLDER TAIL PLATING: TIN

ENVIRONMENTAL  
 OPERATING TEMPERATURE: -40 UP TO 105°C  
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL  
 CURRENT RATING: 20A  
 WORKING VOLTAGE: 300VAC  
 WITHSTANDING VOLTAGE: 1.6KV  
 CONTACT RESISTANCE: 20 mOhm max

STANDARD  
 RoHS CERTIFIED E315414

MECHANICAL  
 PITCH: 7.62MM

SOLDERING: WAVE PROCESS ONLY

PACKAGING: BOX

RoHS Compliant

G			
F			
E			
D	25-FEV-22	PBT -> PA66	AK
C	14-OCT-09	STANDARD	JP
B	23-JUN-09	DESCRIP.: CLOSED	JP
A	05-NOV-08	PDF	JP
REV	DATE	FILE	BY

PROJECTION:

APPROVAL: JHe

GENERAL TOLERANCE  
 .X = +/- 0.2  
 .XX = +/- 0.15

UNIT: MM  
 SCALE:  
 SHEET: 1/1  
 DRAW: MARVIN



DESCRIPTION: SERIE 3134 - 7.62MM CLOSED HORIZONTAL PCB HEADER  
 WR-TBL

WERI PART NO: 691 313 410 0xx

SIZE  
**A4**