




- SPECIFICATION**
1. Rating : DC30V 1.5A.
 2. Contact resistance: $\leq 100m\Omega$.
 3. Insulation resistance: $\geq 100M\Omega$ (DC250V).
 4. Withstanding voltage: 250VAC .
 5. Insertion and extraction force: 5-35N.
 6. life test: 10000 cycles.
 7. Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
 8. Sign"* "is importance dimension.

P.C.B LAYOUT

					TOLERANCE UNLESS SPECIFIED								
					< 1.5: ±0.1mm	ANGULAR ±1°	1						
					> 1.5~5.0: ±0.25mm			NO	DATE	REVISIONS		BY	APPD
					> 5.0: ±0.3mm								
3	CONTACT FOOT	PHOSPHOR BRONZE	5	Ag/Au-Plated	TITLE: USB JACK		UNIT : MM	ROHS COMPLIANT	DWN				
2	COAT	BRASS	1	Ni-Plated	MODEL: USB-111CB-B-CU B		SCALE: 1:1		CHK'D				
1	HOUSING	LCP	1	WHITE	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司				APPD				
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:			REV :A0	