



REV.	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	初始版本	Win	Jerry	2022.09.05
A1	新增包装规范	Win	Jerry	2022.12.19

受控文件
日期: 2023年7月25日

NOTES:

- Mechanical: mating force 7N Max; unmating force 1N Min;
机械测试: 插入力7N Max; 拔出力 1N Min;
- Contact surface should not have burrs; Other areas burr 0.05mm Max.
端子接触面不能有毛刺; 其他区域毛刺不能超过0.05mm
- The dimension marked " * " shall be checked.
标识 " * " 的尺寸为重点管控尺寸
- Harmful material please follow RoHS.
产品需符合RoHS标准.

NO	P/N	Material	Plating
1	922-050-0111	C5191-EH T=0.15,W=12.0	素材
2	922-050-1111	C5191-EH T=0.15mm	Ni 1~3μm, 1 ~ 3μm锡

X± 0.15	X'± 1°	Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司	TITLE: 0.50 mm Female contact		PART NO. 922-050-X111			
X± 0.10	X'± 0.5°		APPD: Jerry 2022.12.19		DWG NO: 922-050-X111			
.XX± 0.05	.XX'± /		CHKD: Jack 2022.12.19			SCALE	SHEET	REV.
.XXX± 0.02	.XXX'± /		DRAW: Win 2022.12.19			1:1	1/1	A1
UNITS:	mm	<small>The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission.</small>						