

Product data sheet

Characteristics

8501KPDR12V63

Relay, Type KP, plug in, tubular, 1HP at 277VAC, 10A resistive at 120VAC, 8 pin, DPDT, 2NO, 2NC, 125VDC coil



Main

Product range	8501K
Product type	Relay
Relay Type	General purpose
Mounting type	Socket
Contact composition	DPDT
[Uc] control circuit voltage	125 V DC
Pilot light	No indicator
Manual operator	Without test button

Complementary

Horsepower rating	1 Hp 277 V AC 0.33 hp 120 V AC
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 10 A 30 V DC resistive control circuit UL 508
Maximum switching voltage	300 V AC 30 V DC
Contact material	Silver alloy (AgNi)
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Tubular
For use with	8501NR51 8501NR52

Environment

Product certifications	UL Listed UL Recognized CSA CE
Height	2.66 in (67.56 mm)
Width	1.40 in (35.56 mm)
Depth	1.40 in (35.56 mm)

Ordering and shipping details

Category	21141 - 8501 KP
Discount Schedule	CP2
GTIN	785901578932
Nbr. of units in pkg.	1
Package weight(Lbs)	3.20 oz (90.719 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.00 in (5.08 cm)
Package 1 width	2.00 in (5.08 cm)
Package 1 Length	3.00 in (7.62 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	60
Package 2 Weight	12.40 lb(US) (5.625 kg)
Package 2 Height	9.00 in (22.86 cm)
Package 2 width	7.00 in (17.78 cm)
Package 2 Length	9.50 in (24.13 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------