


## **TOP VIEW**

## SIDE VIEW

## **BOTTOM VIEW**







Specifications			Notes		Revision History					
Description	Value	Unit	- Notes		Version	ersion Description			Date	Approved
Technology	Electro-Mechanical		1) All dimensions are in mm u	1	Released from Engineering			10/21/2013	J.S	
Resonant Frequency	2,048	(Hz)	2) All parts meet RoHS							
Rated Voltage	12	(V)								
SPL @ 10cm	85	(dBA)								
Coil Resistance	115	(ohm)								
Mount Type	Thru-hole									
Voltage Range	6~18	(V)								
Max Rated Current	40	(mA)								
Housing Material	NORYL				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-25 ~ +70	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-30 ~ +80	°C		Electro-Mechanical Tra	neducor	TE162012-2				
Weight	7	(g)		Electro-iviechanical fransuucei		1 5 1 0 2 0 1 2 - 2				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.