



PCB LAYOUT(Tolerance:±0.05)

**Specifications:**

- Contact resistance: ≤10mΩ
- Insulation resistance: ≥1000MΩ
- Rated voltage: 250V AC DC
- Rated current: 5.0A AC DC
- Withstand Voltage: 1000V AC/minute
- Temperature Range: -25℃ ~ +85℃
- Housing: LCP UL94V-0, BLACK
- Contacts: Brass/MATTE Sn-plated
- Solder Tabs: Brass/MATTE Sn-plated

Poles	Part NO.	Dimension (mm)	
		A	B
1*2	W-3001M02P-0000	3.0	9.65
1*3	W-3001M03P-A000	6.0	12.65
1*4	W-3001M04P-0000	9.0	15.65
1*5	W-3001M05P-A000	12.0	18.65
1*6	W-3001M06P-A000	15.0	21.65
1*7	W-3001M07P-A000	18.0	24.65
1*8	W-3001M08P-A000	21.0	27.65
1*9	W-3001M09P-A000	24.0	30.65
1*10	W-3001M10P-A000	27.0	33.65
1*11	W-3001M11P-A000	30.0	36.65
1*12	W-3001M12P-A000	33.0	39.65

APPROVED:	DATE:	深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: MX3.0SMT-1*XP 卧贴 无柱			
DRAWN:	DATE:	PART. NO. /		UNIT	SCALE
SXA 2016-08-17	2016-08-17	mm	free		FILE NO. Ckmtw-MX-00020 REV. A JK01

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05