



## MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole

### **RF Connectors Technical Data Sheet**

**PE4193** 

#### Configuration

- MHV Female Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry

#### **Features**

- Max. Operating Frequency 300 MHz

- Solder Cup Interface Type
- Solder Attachment
- Bulkhead

- Excellent VSWR of 1.2:1

- Gold Plated Brass Contact
- 30 µin minimum contact plating

### **Applications**

General Purpose Test

Rack and Panel Mount Applications

#### Description

Pasternack's PE4193 MHV female bulkhead connector with solder cup terminal (.380 inch DD hole) is part of our full line of RF components available for same-day shipping. Our MHV female connector operates up to a maximum frequency of 300 MHz and offers excellent VSWR of 1.2:1. This MHV bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Our MHV female bulkhead connector PE4193 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration. Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	MHz
VSWR			1.2:1	
Operating Voltage (AC)			3,500	Vrms
Inner Conductor DC Resistance			2	mOhms
Outer Conductor DC Resistance			1.5	mOhms

#### **Mechanical Specifications**

Size

Length 1.69 in [42.93 mm] Width/Dia. 0.57 in [14.48 mm] Weight 0.029 lbs [13.15 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole PE4193

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole

# RF Connectors Technical Data Sheet

**PE4193** 

#### **Material Specifications**

Description	Material	Plating
Contact	Brass	Gold 30 µin minimum
Insulation	PTFE	
Outer Conductor	Brass	Nickel 100 μin minimum
Body	Brass	Nickel 100 μin minimum

#### **Environmental Specifications**

**Temperature** 

Operating Range

-55 to +155 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole PE4193

URL: https://www.pasternack.com/mhv-female-standard-solder-cup-terminal-connector-pe4193-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

© 2018 Pasternack Enterprises All Rights Reserved

## PE4193 CAD Drawing

MHV Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .380 inch DD Hole

