





A4				<p>台普 ROC PU</p>	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92223P224RS
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw	
A1					ROC PU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION DESCRIPTION	ISSUE		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission					

A		B		C		D		E		F		G	
性能参数													
1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:2.80mm ± 0.10 按压行程:2.80mm ± 0.10 7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10 8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 9. Protection level:IP67 防护等级:IP67 10. Explosion prevention level: IK10 防暴等级: IK10 11. Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C 12. Compression torque: ≤ 3.5N 按压扭力: ≤3.5N 13. Electrical life: 100000 cycles 电气寿命: 100000 cycles 14. mechanical: 500000cycles 机械寿命: 500000cycles 15. Operation method:Self repeating form 操作方式: 自复式 16. Power-frequency withstand voltage: 2000V/1min 工频耐压: 2000V/1min 17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 18. LED lamp lifespan: 40000h LED寿命: 40000h 19. LED color: Red LED颜色: 红色 20. LED Lamp Voltage: 24V LED灯电压: 24V 21. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N													
连接形式													
1. Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20°C Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 Switch function wire: blue wire (NO) yellow wire (NC) 开关功能线材: 蓝线 (NO) 黄线 (NC) 2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极													
A4				 台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92223P224RS		
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw		
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission						
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR							
A		B		C		D		E		F		G	

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
10	luminous zone 发光区	PC 塑胶	1	
9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银
8	Base 底座	PA66	1	
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金
6	Contact material 接触材质	silver alloy 银合金	1	
5	LED Base LED基座	PA66	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
3	Oring O型圈	Silica gel 硅胶	1	
2	Housing 外壳	SUS 不锈钢	1	
1	Key 按键	SUS 不锈钢	1	

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92223P224RS
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					