



NOTES:

1. RATING: 12VDC 50mA
2. CONTACT RESISTANCE: 100mΩ Max
3. INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
4. DIELECTRIC STRENGTH: 250VAC (50/60Hz) FOR 1MIN
5. LIFE TEST: 100,000 CYCLES
6. OPERATION FORCE: 250±80g
7. TRAVEL: 0.25±0.15mm

P. C. B LAYOUT



CIRCUIT



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TPB01-103L1S-RF
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				