



(2.54 mm) .100"

BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:
SS, SD, HSS, SL, SDL,
ESS, ESD

FEATURES

- Low-profile design achieves (3.89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:
Black Liquid Crystal Polymer (BBL, BHS)
Black Glass Filled Polyester (BBS, BBD, BDL)
Temperature Range:
-55 °C to +125 °C
Terminal Material:
Phosphor Bronze or Brass
Plating:
Au or Sn over
50 μ" (1.27 μm) Ni
Lead-Free Solderable:
Yes (BBL, BDL, BHS-S)
No, Lead Wave only (BBS, BBD, BHS-N)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note:
Some lengths, styles and options are non-standard, non-returnable.

