

BU-P72922-@ (Safety 2mm Banana Jack)

- Accepts shrouded or non-shrouded 2mm banana plugs
- Overall length is: 1.2" (30mm), Bezel Diameter is .39" (9.9mm), Bezel height above panel is: .08" (2mm)
- Wire connection: .187" (4.7mm) Quick Connect or solder
- Panel Thickness up to and .50" (12.7mm), Recommended Mounting hole diameter is: .319" (8.1mm)
- Material: Contacts— Nickel Plated Brass Insulator— Polyamide
- Color: The "@" in the model number represents color. Available colors are:

-0 Black, -2 Red

- Ratings: 600 V. CAT II, 10 Amps.
- Temperature: -40°C to 90°C
- RoHS 2 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld. 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524