



Pre-assembled relay module PRS..., Screw connection, Consisting of: relay socket base, power contact relay, pluggable display/suppression module and holding clip, 4 CO contacts, Input voltage: 220 VDC

### Business data

Article number	<u>15727.2</u>
Article name	PRSU 4/220V DC
GTIN (EAN)	4044211138479
Packaging unit	1
Quantity unit	PC
Weight per piece (not including packaging)	87.9 g
Weight per piece (including packaging)	98.67 g
Unit of weight	G
Customs number	85364900
Country of origin	CN
Product description	Complete module

### Technical data

#### Dimensions

Length	76 mm
Width	27.1 mm
Height TS 35 / 7.5 with BA	85 mm

#### Ratings

Rated voltage Un	220 VDC -
Overvoltage category	III
Contamination degree	3

#### Connection data

Connection principle	Screw connection
Wire cross-section single core (rigid), min.	0.2 mm <sup>2</sup>
Wire cross-section single-core (rigid), max.	2.5 mm <sup>2</sup>
Wire cross-section stranded, min.	0.2 mm <sup>2</sup>
Wire cross-section stranded, max.	2.5 mm <sup>2</sup>
Wire cross-section stranded with wire-end ferrules, min.	0.2 mm <sup>2</sup>
Wire cross-section stranded with wire-end ferrules, max.	1.5 mm <sup>2</sup>
Stripping length	8 mm
Torque	0.8 Nm

#### Input data

Drop-out voltage	22 VDC
Operating range	ab 165,0 VDC
Power consumption	0,75 W

#### Output data

Switching voltage / switching voltage max.	240 / 240 VAC
Continuous current max. / Inrush current max.	6 / 12 A
Contact configuration	4 CO contacts
Switching capacity, max.	1500 VA
Electrical lifespan (AC1)	1,5x10 <sup>5</sup>
Mechanical lifespan	30x10 <sup>6</sup>
Contact load, min.	120 mW
Bounce time at close of the NO/NC contact	6/8 ms

### Technical data

#### Materials

Contact material	AgNi 90/10
Flammability class UL 94	V-0
Working temperature, min.	-25 °C
Working temperature, max.	70 °C

#### Further technical data

Degree of protection	IP20
Status display	✓
Insulation voltage coil/contact	2,5 kV
Free-wheel diode	✓
Response/release time	10 / 18 ms
Insulation voltage contact/contact	1,2 kV
Test button	✓
Vibration resistance NO/NC	7/4 g
Pinning	2.8 (fast-on) mm

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

15727.2 PRSU 4/220V DC



---

## Approvals

---

### Standards and regulations

---

CE compliant	yes
--------------	-----

---

---

### Media

---



### Accessories

#### Cross-connector



External cross-connector insulated, for relay socket base PRS 4/6-pole, can be shortened, Voltage: 250 V, Current: 10 A

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15778.2</u>	AQI/PRS/6 BK	4044211133993	20 ST

#### Screwdriver



Screwdriver with bare blade, Colour: Black-grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1086.0</u>	SDB 0,6x3,5	4044211014797	1 ST

#### Relays



Plug-in industrial relays with power contacts, 4 CO contacts, Test button, Mechanical switching position indicator, Polarity A1+, A2-, Input voltage: 220 VDC

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15368.2</u>	PRS 4/220V DC	4044211078591	1 ST

#### Holding clamp



Relay holding clip, With eject, Suitable for relay socket base PRS 4, for industrial relays

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15140.2</u>	PRS C4	4044211046224	1 ST

#### Insert modules

## 15727.2 PRSU 4/220V DC



Insertion module, Suitable for relay socket base PRS, LED red status display

Article number	Article name	GTIN (EAN)	Packaging unit
<u>15142.2</u>	PRS LED(RD) 230V AC	4044211046255	1 ST