



LAYOUT SHOWN AS EXAMPLE

Keying Shown as example

| Connector dimension | |
|---------------------|----------|
| Dim | Nominal |
| ØS | 35.7 Max |
| Z' | 31.5 Max |
| VV THREAD | M25x1-6g |

CHARACTERISTICS

- Standard : Based on MIL-DTL-38999 Series III
- Shell Material : Composite
- Shell Plating : Olive drab Cadmium
- Insulator : Thermoplastic
- Contacts : Copper Alloy
- Seals & Grommet : Silicon Elastomer
- Contact Plating : Gold over copper Alloy 0.8µm minimum
- Durability : 500 Mating cycles
- Delivered with Souriau contacts and Accessories
- Temperature Range : -65°C to +175°C
- Salt Spray : 2000 hours
- Mass : 42.6 g ± 10%

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| | |
|---------|-----------------------------|
| Country | Jurisdiction & Control List |
| FR | Not Listed |

PN: 8D517J75BB

| | | | |
|--------------|------------|--------------------------|-------------------------|
| A | 14-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |

| | | | | | | | | | |
|----------------|-------------------------|---|---|----|---|----|---|---|------------------------------------|
| BASIC SERIES: | 8D | 5 | - | 17 | J | 75 | B | B | ORIENTATION : B |
| SHELL TYPE : | Plug with RFI Shielding | | | | | | | | |
| CONTACT TYPE : | Standard Crimp Contact | | | | | | | | |
| SHELL SIZE : | 17 | | | | | | | | |
| PLATING : | J = Olive drab Cadmium | | | | | | | | |
| | | | | | | | | | CONTACT TYPE : SOCKET(500 Matings) |
| | | | | | | | | | CONTACT LAYOUT : 17-75 |

| | | | |
|----------------|---------------------------------|--------------------------------|---|
| TITLE | Composite Plug 8D series | | |
| SCALE | NA | General linear Tolerances: ±-- | NPRDS / PROJECT 859 |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | A3 | | SOURIAU DRG N° 8D517J75BB-C |
| | | | SHEET 1/2 |

Contact Layout

75



2#8 Triax

| 17-75 | | |
|-------|---|-------|
| Ctc | X | Y |
| A | 0 | 4.75 |
| B | 0 | -4.75 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D517J75BB

| | | | |
|----------------|------------------------------------|--------------------------------|---|
| A | 14-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |
| TITLE | Composite Plug 8D series | | |
| SCALE | | General linear Tolerances: ±-- | NPRDS / PROJECT 859 |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D517J75BB-C | | SHEET 2/2 |