

## **615** Plug

12-pin **EMC - Shielding** 

## **Technical Data**

number of pins temperature range -20 °C to 130 °C clamping range Ø 8.5 mm to Ø 10.5 mm when connected IP 66/67 protection type

**Electrical Data** signal max. 5 A\* 63 V (AC/DC) 1500 V rated voltage rated insulation voltage (L-L)

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category 3 III max. height for operation 2000 m

## **Material**

zinc diecast / nickel plated PBT, PA, UL 94/V0 housing

insulation insert

seals FKM clamp ring plastic

Contacts (not part of product contents)

Tools (not part of product contents)

E ST B 002 NN 00 33 0001 000 ESB002N00330001000



**Contact Arrangement** mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mall: intercontec@te.com Web: www.intercontec.biz





\*for max. wire cross-section pay attention to the cross-section of used contacts