

# 723 htec Extension

## speedtec

insulation insert Code 1 male **EMC - Shielding** Earth-to-Housing Connection according to VDE 0627 **Protection Against Contact according to VDE 0623 Electrically Protective Separation according to VDE 0140** 

#### **Technical Data**

number of pins 5 (4+PE) power -20 °C to 130 °C temperature range Ø 14.0 mm to Ø 17.0 mm clamping range protection type when connected IP 66/67

**Electrical Data** signal power max. 30 A\* max. 1.2 A\* rated current rated voltage 850V/DC 630V/AC 50V/DC 30V/AC rated insulation voltage (L-L) 1500 V 6000 V

500 mating cycles

#### Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation III 2000 m

#### Material

zinc diecast / nickel plated PA 6.6 mod., UL 94/V0 housing insulation insert clamp ring brass / nickel plated

Contacts (not part of product contents)

Tools (not part of product contents)

### H 52 A 008 NN 00 59 0100 000 H K A 008 N 00 59 0100 000



**Contact Arrangement** mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and degree predictations. latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mall: intercontec@te.com Web: www.intercontec.biz

03.09.201

ssue:



