


6

5

4

3



2

1

F

Е


D

С

В


A

SHEET 1 OF 1



7

6



5

TBR - 00 - 197 - XX - XX - LF (A) (B) (C) (D)					
A. Pitch					
A. Pitch - 197=.197(5.00) cl B. No. of Positions - 02-24 C. Color - GR= Green (Standard) - BK= Black - BL= Blue - WH= White - GY= Grey - OR= Orange - YW= Yellow - RD= Red - BB= Brown					
D. Lead Free					
Specifications: Current Rating: 10 Ampere Voltage Rating: A 250V Wire Range: 12-26 AWG Insulation Resistance: 500Mohm/ 500V Dielectric Withstanding Voltage: AC 2500V/1 minute Temperature Range: -33°C to +105°C Max Torque: 3.51b-in (4.03kgf.cm) Strip Length: .236315 (6-8mm) Materials: 1. Body: PA66 (Nylon), UL94V-0 2. Screw: M2.5, C1018 Steel, Blue Zinc Plated 3. Contact: Brass, Nickel Plated 4. Terminal: Brass, Tin Plated					
Tails may be clipped to acheive specific dimensions.					
Products cut to specific sizes are uncancellable/ nonreturnable. Parts are subject to change without notice.					
DRAWN EOW 04/16/14					
CHECKED GWE 04/16/14					
MFG APPR.					

TITLE: TBR-00-197 Series

1

SIZE DWG. NO.

SCALE 6:1

FG APPR. DDRESS:

2533 Centennial Blvd. Jeffersonville, In 47130 Phone: 812-670-4174 Fax: 812-670-4175 E-Mail: mle@mlelectronics.com

2

8

8

F

F

D

≁

С

В

PROPRIETARY AND CON

4

ROME		UNLESS OTHERWISE SPE DIMENSIONS AR INCHES TOLERENCES: ONE DECIMALS 3 TWO DECIMAL ±	1
	PROPRIETARY AND CONFIDENTIAL	THREE DECIMAL	
	HE INFORMATION CONTAINED IN THIS RAWING IS THE SOLE PROPERTY OF fajor League Bectronics, ANY	FOUR DECIMAL :	+
	REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF Major League Bectronics IS	NEXT ASSY	ι
	PROHIBITED.	APPLICATION	

	INCHES TOLERENCE ONE DECIM/ TWO DECIM/ THREE DECI FOUR DECIN	ALS ±.100 AL ±.100 MAL ±.005	INTERPRET TOLERANG MATERIAL
DLE	NEXT ASSY	USED ON	FINISH
	APPLICATION		DO N

SS OTHERWISE SPECIFIED:	
NSIONS ARE IN ES RENCES: DECIMALS ±.100 DECIMAL ±.100 E DECIMAL ±.005 DECIMAL ±.002	INTERPRET GEOMETT TOLERANCING PER: MATERIAL
ASSY USED ON	FINISH

ECIMAL ±.100 DECIMAL ±.005 ECIMAL ±.002		INTERPRET GEOI TOLERANCING
	MATERIAL	
5Y	USED ON	FINISH

