







APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	02/15/12	
A		REDRAWN	02/17/12	
B		UPDATED DRAWING	9/21/17	HR/RC1



**SPECIFICATIONS:**

Material:  
 Insulator: LCP, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Copper Alloy  
 Shell: Stainless Steel, Matte Tin plated  
 Plating:  
 Gold Flash over Nickel underplate on contact area,  
 Gold Flash over Nickel underplate on solder tails  
 Electrical:  
 Contact resistance: 30 mohms max.  
 Insulation resistance: 1,000 Mohms min.  
 Dielectric withstanding voltage: 100 VAC for 1 minute  
 Environmental:  
 Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			
APPROVALS		DATE	
DRAWN	TW	02/15/12	
CHECKED	AY	02/15/12	
APPROVED			
TITLE		MICRO USB, TYPE B, SINGLE PORT RIGHT ANGLE, SMT, TAPE AND REEL	
SIZE	PART NO.	REV.	
X	MCR-B-S-RA-TSMT-NP-CS2-T/R	B	
REF:	S00015C	SCALE:	NTS
		SHEET 1 OF 1	