
## **RoHS COMPLIANT**



## **Electrical Characteristics**

Nominal Impedance: Non constant

Operating Voltage (rms): 500 V maximum at sea level Insulation Resistance: 5000 megohms minimum

**Mechanical Characteristics** 

500 cycles minimum Mating Cycles:

**Environmental Characteristics** 

Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Dielectric	POM
3	Contact	Brass,Nickel Plated

CAD Issue	SN	2	23 Jan 02
First Issue	PDC	1	25 Aug 00
DESCRIPTION OF REVISION	APPVD	ISS	DATE



**Cinch Connectivity Solutions** 7-13 Russell Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK.

Tel. +44 (0) 1245 359515 Fax: +44 (0) 1245 358938

	SCALE: Not To Scale	DRAWN BY:	S Nash		
	DIMENSIONS: mm	CHECKED BY:	P Couzens		
	TOLERANCES: ± 0.2mm unless	APPROVED BY:	P Couzens		
	otherwise stated	DATE:	23 Jan 03		

TITLE:

Euro Plug to BNC Plug

PART NUMBER:

**VA230** 

PAGE: 1 of 1