



### **SUMMARY**

# Wires

Coax 1



Image is for illustrative purpose only

Series 01

Termination type Female solder

IP rating 50

AWG wire size 0.00 - 0.00 Cable Ø 0.00 - 0.00 mm

Status Obsolete

**Download** 

Request a quote

Catalog

### **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model ECP.01\*: Fixed receptacle, nut fixing (back panel mounting)

Keying Circular, female

Housing Material Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces

Weight 1.04 g

**Performance** 

Configuration 01.250 : 1 Coax (50 Ohm)

Insulator

**Rated Current** 

**Specifications** 

Contact Type: Solder


Others

Endurance (Shell): 1000 mating cycles

Salt Spray Corrosion: >144 hr

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# **DRAWINGS**





#### **Dimensions**

	А	Emax	L	М	e
mm.	7	3.5	10.5	5.7	M5x0.5
in.	0,28	0,14	0,41	0,22	

# **RECOMMENDED BY LEMO**

**Tools** 

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.