



MODULAR JACKS AND PLUGS:

GSLGX Series Ganged

Modular Jack with LED, Tab Down

Product Features

- Easy Viewing LEDs to act as Power/Transmit Indicators
- Snap in Retention Tabs
- Available Fully Shielded for EMI/RFI Protection
- CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing Material

PBT Thermoplastic, with Glass-fiber Reinforcement,
UL 94V-0 Rated

Contact Material

Phosphor Bronze

Plating

Gold Plated Over Nickel in Contact Area, Tin in Solder Area

Electrical Characteristics

Current Rating

1.5A

Voltage Rating

125V DC

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number



Part Number Builder

<input type="text"/>	-	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
Series		Shield Option	No. of Port	No. of Positions & Contacts	Ground Pin Spacing	LED Color Option

Series

GSLGX - Ganged Modular Jack PCB Mount

Shield Options

N - Non-Shielded

NS7 - Fully Shielded with Top & Side Grounding Tabs

Number of Ports

4 - 4 Port

Number of Positions / Contacts

88 - 8 Positions / 8 Contacts

Ground Pin Spacing

Blank - Non-Shielded

3.05 - 3.05mm Ground Pin Spacing (Fully Shielded Only)

LED Color

G/Y - Green/Yellow

Y/G - Yellow/Green

Contact Kycon for Additional LED and Plating Options

GSLGX Series

Dimensions in mm

