

www.lemo.com

PSA.1E.250.CTLC35Z

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 1E

Termination type Female solder Coaxial

IP rating 68 mated (mating interface)

AWG wire size 0.00 - 0.00

Cable Ø 3.10 - 3.50 mm

Status Active

Matching parts FFA.1E.250.CTAC35

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model PSA*: Fixed receptacle, nut fixing, cable collet

Keying Circular, female

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE

AMS QQ N 290] brass mid pieces

Variant Z: Nut for fitting a bend relief

Performance

Configuration 1E.250 : 1 Coax (50 Ohm)

Insulator T: PTFE
Rated Current 12 Amps

Specifications

Contact Type: Coaxial 50 Ohm (Solder)

Contact Dia.: 0.9 mm (0.035in) Bucket Dia.: 1 mm (0.039in) Vtest: 3000 V (AC), 4200 V (DC)

Impedance: 50 Ohm VSWR: 1.01 + 0.23 * f/GHz

Cable type: RG 178 B/U, RG 196 A/U, RG 188 A/U, RG 316 B/U, RG 174 A/U, HF-2114, RG 122 /U

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Others


Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +200°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS







Dimensions

	А	В	E	L	м	S 1	S2	\$3	e
mm.	20	21.5	9	45	4.5	14.5	9	19	M16x1.0
in.	0,79	0,85	0,35	1,77	0,18	0,57	0,35	0,75	

RECOMMENDED BY LEMO

Tools

Spanner wrench: DCD.1E.ZZZ.PA090

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

CCX.75.040.195327G	PVC	Grev	
00/11/510 1011/552/0	1. 10	dicy	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.