



NOTES

1. MATERIAL: COPPER ALLOY, t=0.25mm
2. FINISH: PRE-TIN PLATED
3. RECOMMENDED LENGTH OF WIRE STRIP: 5.0-5.6

PRE-RELEASE
REFERENCE
USE ONLY

NO.	ENG. NO.	TYPE	DESCRIPTION	CABLE SIZE(mm ²) AVS, AVSS	DIMENSION			
					W1	H1	W2	H2
1	35407-6702	S	.090 SEALED FEMALE TER'L	0.3 - 0.5	2.5	2.2	5.1	4.2
2	35407-6802	M	.090 SEALED FEMALE TER'L	0.85-1.25	2.6	3.0	5.2	4.7

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: OBSOLETE PART NUMBER		molex	
DIMENSION UNITS: mm		SCALE: 5:1			
GENERAL TOLERANCES (UNLESS SPECIFIED)				.090 SEALED FEMALE TER'L	
				PRODUCT CUSTOMER DRAWING	
4 PLACES ±				EC NO: 655042	
3 PLACES ±				DRWN: ABHISP1 2021/03/01	
2 PLACES ±				CHK'D: GGA 2021/03/01	
1 PLACE ± 0.25				APPR: GGA 2021/03/01	
0 PLACES ±				INITIAL REVISION:	
ANGULAR TOL ± 1.0°				DRWN: BCYOON 1998/04/10	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				APPR: CWLEE 1998/04/10	
THIRD ANGLE PROJECTION		DRAWING		SERIES	
DRAWING		A3-SIZE		35407	
MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
SEE TABLE		GENERAL MARKET		1 OF 1	