




N ATTENUATOR 30 DB 18 GHZ 2W

PAGE 1/2 ISSUE 17-07-15A SERIES ATTENUATOR PART NUMBER R414730150



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact Female center contact	STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER	PASSIVATED GOLD OVER NICKEL GOLD OVER NICKEL	
Outer contact	STAINLESS STEEL	PASSIVATED	
Insulator Gasket	PTFE SILICONE RUBBER		
Substrate	ALUMINA CERAMIC		
Resistor Others parts	THIN FILM STAINLESS STEEL	•	



Connectors

Weight

Technical Data Sheet

N ATTENUATOR 30 DB 18 GHZ 2W

PAGE 2/2	ISSUE 17-07-15A	SERIES ATTENUATOR	PART NUMBER R414730150
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

N

DC - 18	GHz
50	Ω
30	dB
50	W
2	W (Free Air Cooled)
	W (Conduction Cooled)
	50 30

MECHANICAL CHARACTERISTICS


Male Female

MIL-C 39012



Operating temperature range -55/+125 °C

Storage temperature range -55/+125 °C



SPECIFICATION

OTHER CHARACTERISTICS