



			1		
P	art Number:		DRAWN	4/42/2040	
CMAE		1400 1	CJ	4/13/2018	
	SM450	0408-2	CHECKED	4/27/2018	
			C.H.		
D	escription:	c Speaker	APPROVED	4/27/2018	
	Dynami		C.E.	4/2//2018	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Items	Specifications	Conditions						
Sound Pressure Level	90	dB (@ 10cm), Avg.						
Resonant Frequency	450	Hz						
Frequency Range	450 ~ 10,000	Hz		REVISION HISTORY				
Nominal Power	2	W	REV	DESCRIPTION	DATE	APPROVED		
Max. Power	3	W		Released from Engineering	4/27/2018	C.E.		
Impedance	8	Ω	1	Updated terminals	2/3/2021	J.S.		
Cone Material	Mylar		,	NOTES				
Mount Type	Flush Mount			All dimensions are in mm unless otherwise noted				
Storage Temperature	-20 ~ +55	°C		2) All tolerances are ± 0.3 mm unless otherwise noted				
Operating Temperature	-20 ~ +55	°C		3) All parts meet RoHS				
Weight	10.8	g		4) Subject to change or redrawn without notice				