


			1	
	Part Number:		DRAWN	2/10/2017
	CM20	0408-1	CJ	3/10/2017
	500280		CHECKED	10/5/2017
			P.D.	
	Description:	namic Speaker	APPROVED	10/5/2017
	Waterproof Dy		C.E.	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View




-20 ~ +55

7.3


Operating Temperature

Weight

Side View



Bottom View



Items	Specifications	Conditions	7					
Sound Pressure Level	90	dB (@ 10cm), Avg.	REVISION HISTORY					
Resonant Frequency	480	Hz	REV	DESCRIPTION	DATE	APPROVED		
Frequency Range	480 ~ 10,000	Hz		Released from Engineering	10/5/2017	C.E.		
Nominal Power	1.5	W	1	Added polarity marking	10/25/2017	C.E.		
Max. Power	2	W	2	Update markings	2/28/2018	C.E.		
Impedance	8	Ω	3	Added mounthing hole dimensions	9/3/2019	C.E.		
Cone Material	Mylar		4	Updated Resonant Frequency	3/25/2020	J.S.		
Mount Type	Frame Mount			NOTES				
IP Rating	IP67			All dimensions are in mm unless otherwise noted				
Storage Temperature	-20 ~ +55	°C	2) All tolerances are ± 0.3 mm unless otherwise noted					

3) All parts meet RoHS

4) Subject to change or redrawn without notice