





Rev	AWO #	Description	Date	Appr
-		RELEASED	3/16/15	

6 5 4 3 2 1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



**SPECIFICATIONS:**  
 Material: HI-temp thermoplastic, rated UL 94V-0  
 Insulator color: Natural  
 Actuator: HI-temp thermoplastic, rated UL 94V-0, Color: Black  
 Contacts: Phosphor Bronze  
 Holddown: Brass, Tin plated  
 Plating: Tin over Nickel underplate overall  
 Electrical:  
 Current rating: 0.5 Amps max  
 Contact resistance: 30 mohms max  
 Insulation resistance: 100 Mohms min  
 Dielectric withstanding voltage: 250V AC for 1 minute  
 Temperature Rating:  
 Operating temperature: -25°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant

Positions: 03 thru 61  
 A= .020 [0.50] x No. of Spaces +.283 [7.20]  
 B= .020 [0.50] x No. of Spaces + .043 [1.10]  
 C= .020 [0.50] x No. of Spaces  
 D= .020 [0.50] x No. of Spaces + .201 [5.10]

**ADAM TECH**  
 909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

**ZIF FLEX CIRCUIT CONNECTOR, SMT TYPE**  
**SIDE ENTRY, LOWER CONTACT**

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØXX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010
APPROVALS	DATE
DRAWN AY	3/16/15
CHECKED GC	3/16/15
APPROVED	

SIZE	PART NO.	REV.
X	PCA-6-LA-XX-HL-3	-
REF:	S00163C	SHEET 1 OF 1
SCALE:	NIS	

**A**

**B**

**C**

**D**

6 5 4 3 2 1

