

## **SUMMARY**

#### # Wires

Coax 1

Image is for illustrative purpose only

Series 2B

Termination type Male solder Coaxial

IP rating 50

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status Active

### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

### **Mechanics**

Shell Style/Model \*:

Keying

Housing Material Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces

Weight 1.63 g

### **Performance**

Configuration

Insulator L: PEEK (UL 94 / V-0/1.5)

**Rated Current** 

## **Specifications**

Contact Type: Solder

#### **Others**

Endurance (Shell): 5000

Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms]

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz)

# **DRAWINGS**



# **RECOMMENDED BY LEMO**

### **Tools**

Spanner wrench: <u>DCD.2B.ZZZ.PA120</u>