


7-16 FEMALE COAXIAL TERMINATION 6 GHZ 100W







7-16 FEMALE COAXIAL TERMINATION 6 GHZ 100W

PAGE 2/2	ISSUE 08-11-19B	SERIES TERMINATION	PART NUMBER R404777000
-----------------	------------------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	100 W (Free Air Cooled)	
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	7/16	Female	IEC 169-4
Weight	1 243,4399 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION