

T	<u>م</u>	п	m	O







Keying Shown as example

Connector dimension

Dim

Nominal

CHARACTERISTICS

ω

-Standard : Based on MIL-DTL-38999 Series III

	-Stanuaru . Baseu on n	IIL-DIL-30333 Jelles III		L L	2						
\frown	-Shell Material	: Composite			Р	3.25±0.2				COUDIALI shal	l not ha liabla far an
	-Shell Plating	: Nickel		-	PP	4.39±0.2					l not be liable for an e of the Products wl
	-			-	R1	24.61					is sued by either o
	-Insulator	: Thermoplastic		-	R2 S	23.01 31±0.3				•	sional recommenda
	-Contacts	: Copper Alloy		ŀ	V'	19.5+1.4/-0				(profes	
	-Seals & Grommet	: Silicon Elastomer		ł	w'	2.1/3.65					Count
\sim	-Contact Plating	: Gold over copper Alloy 0.8µm minir	num		Z'	32 Max					FR
	-Durability	: 500 Mating cycles		L	VV THREAD	M22x1-6g				_	
	-Delivered without Sou	iriau contacts								F	N: 8D015N
	-Temperature Range	· -65°C to +200°C									
	-Salt Spray	: 2000 hours						A	12-10-2016	First Release	
	-Mass	: 18 g ± 10%						ISS	DATE	Latest modificat	ion - by
		-						Design	ed By:	Date	:
									TITLE		Composite
	BASIC SERIES:	8D 0 - 15	M 05	S A	L			SCA	ILE	$= \bigcirc$	General linear Tolerances:
	SHELL TYPE : Square	lange Receptacle				Delivered W/	O Contacts	N	A	$\neg \Psi$	±
	CONTACT TYPE : Sta	ndard Crimp Contact				ORIEN	TATION : A	50	URIAU	\^/\^/\^	.SOURIAU.C
	SHELL SIZE : 15				CONTAC	CT TYPE : SOCKET(50	0 Matings)	30	UNIAU		1.300NIA0.0
	PLATING : M =	Nickel				CONTACT LAYO	OUT : 15-05	FORM	ИАТ		SOURIAU
			I					A	3		8D015M
L	Н	G	F			E	1	D		С	
						V					

0		Φ		А		1	
						4	
LAY	YOUT SHOWN AS EXA	MPLE				3	
RIAU shall not be liable for any non-conformity or damage ue to a use of the Products which does not comply with ecifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed PN: 8D015M05SAL							
ase modificatio	on - by		0.0700		MOD N°		
Date:	Composite	Receptac	customer le 8D serie				
Ð	General linear Tolerances: ±	NPRDS / PROJECT 859					
WWW.SOURIAU.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission							
	SOURIAU I 8D015M0				SHEET 1/2		
С		B		А		J	

		G	н г	m		0	
		Contact Layout					Panel Cutou
4	د. 	$E \bigoplus_{r,y} E \bigoplus_$			Λ	SQUARE FLANGE RECEPTACLE REAR MOUNTING	(TYPE 0)
		X-axis Y-axis (mm) (mm) +.000 (0.00) +.100 (2.54) +.174 (4.42) +.024 (0.61) +.094 (2.39) 148 (3.76) 094 (2.39) 148 (3.76) 174 (4.42) +.024 (0.61)			∑ ₹		ØT
ى نى							Dim ØA ØAA R1 ØT
						due to a use the Specificatior	I not be liable for any e of the Products wh ns issued by either of sional recommendat
0						D	Countr FR PN: 8D015W
						2016 First Release	
					ISS DA Designed By:	TE Latest modificati Date:	
					TITLE		Composite
_ _					SCALE NA	$\bigcirc \bigcirc$	General linear Tolerances: ±
					SOURI	AU WWW	.SOURIAU.C
					FORMAT A3	I	SOURIAU 8D015M0
	Н	G	F	E	D	C	

