
	т.	m	C	D	0			•
Z'	ØS							
		I			LAY	OUT SHOWN AS EXAMPLE		
	Keying Shown a	as example						
CHARACTERISTICS-Standard : Based on MIL-DTL-38999 Series III-Shell Material: Composite-Shell Plating: Olive drab Cadmium-Insulator: Thermoplastic-Contacts: Copper Alloy		Connector dimensionDimNominalØS35.7 MaxZ'31.5 MaxVV THREADM25x1-6g			due to a use the Specifications	not be liable for any non-co of the Products which does issued by either of the Part onal recommendation, tech	not comply with ties or by a third party	
-Seals & Grommet: Silicon Elastomer-Contact Plating: Gold over copper Alloy 0.8μm minimum						Country FR	Jurisdiction & Control List Not Listed	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories					F	PN: 8D517J06B	В	
-Temperature Range : -65°C to +175°C -Salt Spray : 2000 hours				A 14-10	-2016 First Release			
Mass : 35.5 g ± 10%			-	ISS DA Designed By:	TE Latest modificatio Date:	n - by	CUSTOMER DRAWING	MOD N°
				TITLE		Composite P	lug 8D series	
BASIC SERIES: 8D 5 - 17 J SHELL TYPE : Plug with RFI Shielding - 17 J	06 B B			SCALE NA		General linear Tolerances: ±	NPRDS / PROJECT 859 This document is the p	ronerty of
CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 17		O CONTACT TYPE : SOCKE	RIENTATION : B	SOURI	AU WWW.	SOURIAU.COM	it must not be repro	luced or
PLATING : J = Olive drab Cadmium			LAYOUT : 17-06	FORMAT A3		SOURIAU DRG 8D517J06BB	i N°	SHEET 1/2
							-C	-, -

	τ	G		г	m	D	0	
		Contact Layout						
4		$-x \qquad \qquad$	+X					
		Contacts (Insert arrangement 17-6) Contact Location						
ى		B +241 (6.12) +.000 (0.00) D -241 (6.12) +.000 (0.00) E 241 (6.12) +.000 (0.00) E 121 (3.07) +.209 (5. F +.000 (0.00) 241 (6.12)	31) 00) 12) 00) 31)					
	Sheil Arrangen size no. 17 -6							
							SOURIAU shall not be lia due to a use of the P the Specifications issued l (professional rec	Products w by either c
2							DNI 9	Count FR 3D517
							D-2016 First Release ATE Latest modification - by Date:	
						SCALE	Gene	Compo
_						NA SOUR		± RIAU.C
						FORMAT A3	80	URIAU D517J
	Н		G	F	E	D	C	



 \triangleright

σ