

Φ		А				
				4		
S EXAMPLE				3		
			]			
which does not	any non-conformity or damage which does not comply with					
er of the Parties or by a third party dation, technical notice.)						
Intry Juri						
	Not Listed					
SW43SEL						
	CUSTOMER D		MOD N°	—		
m Receptacle 8D series						
ar	NPRDS / PROJECT					
	859			1		
COM This document is the property of SOURIAU it must not be reproduced or						
	communicated without permission					
U DRG N N43SEL-C			SHEET 1/2			
B		A				

	т	۵		п	т			0	
4		Contact Layout					JAM NU	Panel cutout	Ā
	Contact position ID         X-axis (mm)           A         -0.696 (1.75).           B         + 203 (5.16).           C         + 3.24 (8.23).           D         + 4.24 (10.77).           E         + 4.93 (12.52).           F         + 5.531 (13.49).           G         + 5.31 (13.49).           H         + 4.93 (12.52).           J         + 4.24 (10.77).	Y-axis (mm)         Contact position ID         X-axis (mm)           +.531 (13.49)         Z        069 (1.75)           +.425 (12.57)         a         +.172 (4.37)           +.425 (10.80)         b         +.258 (6.55)           )         +.326 (8.28)         c         +.344 (8.74)           )         +.026 (5.571)         d         +.344 (8.74)           )         +.069 (1.75)         g         +.172 (4.37)           )        069 (1.75)         f         +.000 (0.00)           )        205 (5.211)         g        172 (4.37)           )        205 (5.211)         g        172 (4.37)	+ 344 (8.74) + 172 (4.37) + 000 (0.00) - 177 (4.37) - 344 (8.74) - 344 (8.74) - 344 (8.74)					ØC >	
ω	K         + 324 (8.23)           L         + 203 (5.16)           M         + 000 (0.00)           N         - 203 (5.16)           P         - 324 (8.23)           R         - 424 (10.77)           S         - 493 (12.52)           T         - 531 (13.49)           U         - 531 (13.49)           V         - 493 (12.52)           W         - 424 (10.77)           X         - 324 (8.23)           Y         - 203 (5.16)	$\begin{array}{cccccccccccccccccccccccccccccccccccc$	+.000 (0.00) +.172 (4.37) +.344 (8.74) +.344 (8.74) +.172 (4.37) 172 (4.37) 172 (4.37) 172 (4.37) +.000 (0.00) +.172 (4.37) +.000 (0.00)					Dim Nominal B 43.43+0/-0. ØC 44.7+0.25/-	
	Shell Arrangement 1 size Arrangement 1 25 -43	Number of Size Service Contact contacts contacts rating 20 16 1 <u>abc.det.gh.kr</u> 23 20 All All others	Supersedes DL K MS20057-43					SOURIAU shall not be liab due to a use of the Pro e Specifications issued by (professional recon	ducts whic either of t
N								PN: 8D	Country FR 725W4
						A ISS Design		Release test modification - by Date:	
_						SC4		Genera Tolera	ninium al linear ances: :
						FORI			IAU.CC RIAU I 25W4
	Н	G		F	E	D		C	

	Ξ		A		
N					4
					3
s whic er of t ndatio untry FR	n, technical n	mply with by a third party	l List		2
			RAWING	MOD N°	
um Receptacle 8D series					
ar :	NPRDS / PROJECT 859				
	COM This document is the property of SOURIAU it must not be reproduced or communicated without permission				
	DRG N°	1		SHEET	
N4	3SEL-C	I		2/2	
	В		А		