



 $\mathbb{B}$ 

**AMM** 

L

## (2.3) 1.3 3.15





Length in

LF Contact Reference

No. Of

Contacts nn


6 ♦

10 🔸


20 ♦

34 ♦

Distance Between



## Recommended PCB Layout



## **Product Specifications**

Material					
Insulator	LCP (Liquid Crystal Polymer) UL94-V0				
Signal Contacts	Signal Contacts  Male : Copper alloy / Ni + Au 0.20µm to 0.40µm max. Female : Copper zinc alloy / Ni + Au 0.20µm to 0.40µm ro				
Fixing Hardware LCP (Liquid Crystal Polymer) UL94-V0					
Electrical Features					
Current rating	UP to 4.8A @ 25°C (PCB to cable 20 pins) Up to 2.5A @ 25°C (PCB to PCB 20 pins)				
Voltage	Voltage  Voltage proof @ sea level: 1000V RMS  Withstanding voltage @ sea level: 600V RMS				
Contact resistance	10mΩ (initial)				
Insulation resistance	> 2GΩ (after conditioning)				
Mechanical Features					
Contact durabitlity	1000 cycles				
Contact force	Engagement: 0.7N max Separation: 0.06N min				
Contact retention	> 6N				

Fixing hardware torque	Screw-Lok: 16cN.m				
Environmental Features					
Temperature cycling	-65°C to +200°C				
Humidity	25°C -65°C / 89% - 94% humidity / 6 days				
Vibration	Sinusoidal vibration: 15g / 10Hz – 2000Hz – 10Hz in 20min / 4h per axis in each 3 axes (total 12h)				
Shock	Peak accelaration: 100g/Normal Duration 6ms; Wave form: sawtooth				

	SHOCK	sawtooth			
Ь	22/06/20	P.K	K.H	A.DL	
Ind	Date	Drawn	Checked	Approved	

NOTE:

- 1. Tape and Reel packaging
- 2. ♦ Configurations are available in stock"
- 3. "Feel free to ask for technical support"

NICOMATIC

www.nicomatic.com

Item: Connector AMM 220 female straight on PCB, nn LF Contacts, R

This docume	ent and	drawings,	sketches	, and s	chematic	drawir	igs are	the prop	erty of
the NICOMA	TIC comp	pany. and	no parts	thereo	f may be	е герго	duced a	nd used	without
the vuitten	CODCOD	t of the	01/DOR   31	4 42+24	11 02 10	N 2			

Catalogue Reference :

A222YnnR

Compliant matrix :	
Customer reference :	TY

General tolerance ±0.2 Scale 3:1

| 1

Page

1/1

Ŋ

۸ ۸